

SMART
SENSOR
BUSINESS

A7 MODULAR SIGNALING COLUMN

Reliable display
of machine conditions



MODULAR, RELIABLE, COST-EFFECTIVE

Optimized processes and increased efficiency thanks to easily recognizable and clear visualization

FLEXIBLE ASSEMBLY OF THE SIGNAL LAMP

The A7 signal lamps enable simple mounting and flexible configuration, while at the same time meeting aesthetic requirements through uniform clear glass optics. The environment is reliably informed about the machine status.

*think*modular.

- Connection of the modules via bayonet lock
- Up to 5 optical modules
- 3 stand heights with plastic foot and module lid
- Preassembled version with 100 mm in the colors red, orange, green
- Transparent calottes
- Cost-effective elements for signaling



Technical data	A7 signal lamp
Lenses	70 mm
Signaling	LED continuous light
Life expectancy	> 100,000 h
Colors	Clear calotte, colored LED (green, red, orange, blue, white)
Voltage	24 VDC \pm 10 %
Current consumption	30 to 50 mA
Temperature	-10 to 60 °C
Degree of protection	IP 66
Connection	Spring-cage terminal
Stand heights	100, 250, 400 mm
Certificates	CE