


ISS 208 (short construction)

Inductive switches

Dimensioned drawing



en 01-2011/09 50114650




M8
2.5mm



10 - 30 V
DC
non-embedded
5 kHz

- Slim and short cylindrical metal housing M8
- Stainless steel housing
- Built-in short circuit protection, inductive protection and polarity reversal protection
- LED for switching state visible from 360°




Tightening torque of the fastening nuts < 10Nm !


- A** Active surface
- B** Yellow indicator diode

Electrical connection


M8 connector



Cable



We reserve the right to make changes • DS_ISS_208_N_en.fm



Accessories:

(available separately)

- M8 connectors (D M8...)
- Ready-made cables (K-D ...)
- Mounting clamp (MC 008...)

Specifications

General specifications

Type of installation non-embedded installation
 Typ. operating range limit S_n 2.5mm
 Operating range S_a 0 ... 2.0mm

Electrical data

Operating voltage U_B 1) 10 ... 30VDC
 Residual ripple σ $\leq 20\%$ of U_B
 Output current I_L ≤ 200 mA
 Open-circuit current I_0 ≤ 10 mA
 Residual current I_r $\leq 100\mu$ A
 Switching output/function .../4NO... PNP transistor, make-contact (NO)
 .../4NC... PNP transistor, break-contact (NC)
 .../2NO... NPN transistor, make-contact (NO)
 .../2NC... NPN transistor, break-contact (NC)

Voltage drop U_d ≤ 2 V
 Hysteresis H of S_r $\leq 5\%$
 Temperature drift of S_r $\leq 10\%$ 2)
 Repeatability $\leq 4.8\%$ 3)

Timing

Switching frequency f 5kHz
 Delay before start-up ≤ 10 ms

Indicators

Yellow LED (visible from 360°) switching state

Mechanical data

Housing stainless steel
 Standard surface plate 8 x 8mm², Fe360
 Active surface PBTP
 Weight (M8 plug/cable) approx. 12g/approx. 70g
 Connection type M8 connector 3-pin or cable: 2m, PVC, 3 x 0.14mm², \varnothing 3.5mm

Environmental data

Ambient temperature -25°C ... +70°C
 Protection class IP 67
 Protective circuit 1, 2, 3
 Standards applied IEC/EN 60947-5-2
 Electromagnetic compatibility IEC 60255-5 1kV
 IEC 61000-4-2 Level 3 air 8kV (ESD)
 IEC 61000-4-3 Level 3 10V/m (RFI)
 IEC 61000-4-4 Level 3 2kV (Burst)

- 1) Observe the safety regulations and installation instructions regarding power supply and wiring; for UL applications: only for use in "Class 2" circuits acc. to NEC
- 2) Over the entire operating temperature range
- 3) For $U_B = 20 \dots 30$ VDC, ambient temperature $T_a = 23^\circ\text{C} \pm 5^\circ\text{C}$
- 4) 1=polarity reversal protection, 2=short circuit protection, 3=inductive protection for all outputs

Order guide

The sensors listed here are preferred types; current information at www.leuze.com.

$S_n = 2.5$ mm	Designation	Part No.
	ISS 208 MM/4NO-2N5-S8.3	50114490



Tables

Reduction factors:
for $S_n = 2.5$ mm

Steel Fe360	1
Copper	0.20
Aluminum	0.25
Brass	0.35
Stainless steel	0.70

Mounting


Non-embedded installation:



Ferromagnetic and non-ferromagnetic materials			
S_n [mm]	D1 [mm]	D2 [mm]	D3 [mm]
2.5	8.0	10.0	4.0

Diagrams

Models with $s_n = 2.5$ mm



ISS 208 (short construction)

Inductive switches

Part number code

I	S	S	2	0	8	M	M	/	4	N	0	-	2	N	5	-	S	8	.	3
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

Operating principle / construction

ISS Inductive switch / short construction

Series

208 Series with M8 x 1 external thread

Housing / thread

MM Metal housing (active surface: plastic) / metric thread

Output function

4NO PNP transistor, make-contact (NO)

4NC PNP transistor, break-contact (NC)

2NO NPN transistor, make-contact (NO)

2NC NPN transistor, break-contact (NC)

Measurement range / type of installation

2N5 Typ. scan range limit 2.5 mm / non-embedded installation

Electrical connection

N/A Cable, PVC, standard length 2000mm

S8.3 M8 connector, 3-pin, axial

Remarks

● **Approved purpose:**

This product may only be used by qualified personnel and must only be used for the approved purpose.
This sensor is not a safety sensor and is not to be used for the protection of persons.

